

## Arova Aqua-Toner F

9006

Water-based dyestuff concentrates for **industry** and **trade**

### PRODUCT DESCRIPTION


#### Product numbers

89154 ff

#### General

Water-based dyestuff concentrates for tinting water-based Arova stain systems.


#### Application area



Tinting of water-based Arova staining systems according to **ARL 113 – Tinting instructions for Arova staining systems**

### PROCESSING

#### Processing instructions



- Please shake the product before use.
- The temperature of the product and object, and the room temperature must be at least + 15 °C.
- Due to the high concentrations, tinting stains with Arova Aqua toners is only recommended for experienced users.
- Use only in combination with the base materials recommended by ADLER.
- Do not use the product as a stain!
- Please observe our **ARL 113 – Tinting instructions for Arova staining systems**.
- Quantity added to stain:  
Total quantity of Arova Aqua toner: max. 20 % by weight depending on the selected stain system.
- Stir in thoroughly!
- Stains tinted with Arova Aqua toners can be processed as specified in the corresponding technical data sheet.
- Prior to applying the stain and the coating, you should always stain a sample on the original wood and treat it with the intended coating material in order to assess the final colour shade.
- Any change in the processing sequence, environmental conditions, non-observance of instructions or the use of products not listed may have an unfavourable effect on the result. Deviations lead to film and adhesion problems.

**Cleaning the working equipment**

With water immediately after use.

**ORDERING INFORMATION****Size of trading unit**

5 l, 11 (depending on the colour)

**Colour shades / Glosslevels****Standard colour(s):**

Braun (89154)  
 Braun (89160)  
 Schwarz (89720)  
 Gelb (89724)  
 Rot (89726)  
 Gelb (89730)  
 Orange (89732)  
 Rot (89733)  
 Braun (89734)  
 Schwarz (89735)  
 Blau (89736)

This technical data sheet applies to all colours of Arova Aqua-Toner F (9006) and colour shade number.

**FURTHER DETAILS****Durability / storage**

Min. 1 year(s) in the original sealed containers.



Make sure the product is protected against moisture, direct sunlight, frost and high temperatures (above 30 °C).

**Safety information**

Further information on the subject of safety during transport, storage and handling as well as disposal can be found in the relevant safety data sheet. The current version can be accessed on the Internet at [www.adler-lacke.com](http://www.adler-lacke.com).

The product is only suitable for the industrial and professional use.

The inhalation of paint aerosols during spray application must generally be avoided. This is ensured by the proper use of a respirator (combination filter A2/P2).